



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

01-17421-001	Central Sys Cntrl, Pentium
01-19336	Cool Plate Assy, High-Eff, STC, EPR
02-01280	pnuem Bd Assy, Coolplate
02-01415	PCB ASSY, Oven Analog
02-01448	Sensor, Board Asst, 9' Cable
02-01581	Sensor, assy, cass, elev, swi
02-01582	Sensor Assy, Elevator
02-02725	Motor, Step 1.8 DEG 12VD
02-03180	Board Assy, Banner Sensor
02-10720	PCB ASSY, Spin Control Board
02-10723	PCB ASSY, Spin Control Driver
02-12783-001	SPIN MTR ASSY,24V,7.2A,FLT SFT
02-12876	PC Assy, Chamber Mother Board
02-13151	PCB ASSY, SERVO INTRC,INTRF,ORB
02-13480-001	PCB ASSY, MULTI I/O, 1 MOTOR
02-14658	Spin Motor Assy, Proc, Chamb, Orb
02-15374	PC Assy, Motor Interconnect
02-15581-001	PCB Assy, Step Motor Ctrl, Orbit
02-15581-002	PCB Assy, Step Motor Ctrl, Orbit
02-15782	Stepper Motor Assy, Disp Arm
02-15999	Stepper Motor Assy, Tpm
02-16135	Stepper Motor Assy, Cass I/O
02-16278	PC Assy, Interface, Mother, Nikon G6
02-17843	Power Supply Module
02-18287	PCB W-Ram & Termin
02-19302-004	Cup Assy, Coat, 150mm, W/T-EBR, KR
02-19599	Mouse Assy
02-22316-001	Paddle Assy, Equipe, 6-8' Wafer
02-22318-004	Paddle Gluement, 4.5'X4.5' SQ
02-25125-001	Pin Lift Assy, Oven, Scorpio
02-25493-002	Sensor Assy, Liq, Det, Disp,Line
02-26251-001	Assy, Stepper Motor, Disp Arm



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

02-27303-001	Motor, Rotary Interface..
02-29758-002	Paddle Assy, 2 Button Type, Utpm
02077718	CX/PO Lens (C1 Plano I-line)
028467G1	XL Aperture Sensor
028944G1	Aperture Blade Motor
03-00538	Cup, Feed, LH
03-02198	Chuck, Delrin, 150mm
03-07163-001	Belt, Wafer
03-07163-002	Belt, Wafer (8.49)
03-07163-003	Belt, Wafer
03-09023-003	Nozz.lin.disp.coat.polyp
03-14401	Pulley, 30T, .250 Bore
03-14405	Paddle, Wafer
03-14697-001	Pin, Wafer Lift, Grooved, SS
03-15356	Enclosure Upper Process Chamber
03-16960-008	End Effector, 5", All
03-17098-001	Housing, Pin Lift
03-17100-001	Lead Screw and Nut
03-18673	Drawing Only - Coater Bowl, FPD 500
03-19306	Ring, EBR, 150mm, 60Deg Noz, Delr
03-19785	Trap, vacuum, 3 ports
03-20349-002	Screw, Chuck FPD 500, Vespel Polyimide
03-20349-003	Screw, Chuck FPD 500, Seitron ESD 420
03-20446	Cup, Vacuum, Robot Arm - Meldin 2001
03-20447	Spacer, Robot Arm - Peek Black
03-21835	Pin, Substrate Lift, APEX 500
03-22694-001	Housing, Arm Lift Seal Holder
03-22782-001	Block, Nozzle, Dev. Mount Apex - Teflon
03-22784-001	Block, Nozzle DI Water, APEX - Teflon
03-22963-001	Shaft, Arm Lift Block Pusher
03-23377-002	Vacuum Chuck, 3.125' diameter
03-24951-001	Tube, Solvent Cup



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

03-27579-001	Plate, Subs Nest, 4.5sq, Orb
04-00031	Bushing, Ball
04-00047	O-ring
04-00097	Cylinder, Air .75BX3.0S, DBL ACT
04-00098	Cylinder, Air .75br, .5stroke,DBl Act
04-00103	Bearing, Linear, Slide
04-00170	Belt 04-00189 Belt, timing
04-00278	Switch,Vac,0-30' HG, 1/4 FNPT
04-00280	Gauge, Vacuum
04-00283	Valve, Toggle, 3W, 10-32ports, NPB
04-00584	Fit, Clpk,Male
04-00887	O-Ring
04-00897	Cool plate flow valve
04-01175	Switch, air pressure, 50' W.C.
04-03377	Fit, Comp, .1/8 x 1/4 F, Teflon
04-04415	Switch, Pressure, 0-3 Psig, Spdt
04-04441	Vibration Mount
04-06330	Air Cylinder
04-06524	Flow Meter 50-500 ML/MIN, EP O-Rings
04-07128-003	Flow Meter, Cup Rinse, Kalrez
04-07385	Bearing,.620DX .25ID, Seal, Flngd
04-07540	Valve, Bellows, 2Way, NC, AP, 1/4c
04-07692	VALVE,AIR ACT,2WAY,NC,3/8C,BN
04-08207	VALVE,CHECK,1/3PSI,1/4C,SS,KR
04-08525	Regulator, Vacuum, V-900, 30 Hg
04-08565	Valve, 3-Way
04-08670	Subbase, single valve w/ flo control
04-08681	Stud, 1/4 T, RA Bail HD,.42 THK
04-08760	BASE,SUB,SNGL VALVE W/FLOW CTL
04-09226	Vacuum Generator
04-09250	Meter, Flow
04-09654	bearing, ball 1.0x1.500x.25



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

04-09655	bearing, ball,.75x10.00x156STL
04-12858	Valve, Solenoid, 3-Way
04-12939	Fitting. Elbow, 10-32x1/8 barb, nylon
04-14903	Bearing
04-15007	VALVE CHECK,1/3 PSI, 1/4FPT
04-15224	Valve, Flow CTL, 10-32F Ports, SS
04-15287	Bearing, Dispense arm
04-15528	Fitting Quick Disconnect Stem 1/16
04-15596	Fitting, One-Touch, 1/8mnpt (package of 10)
04-15597	Fitting, One-touch, 10-32UNF, (Package of 10)
04-15598	Belt, Timing, 1/4W, .08P, 100G, URE
04-16057	bearing, ball .500DX.25IDX.22W 04-16297 Fitting, 1 touch, Elbow
04-16369	Tubing 3/32 O.D. Per Foot
04-17222	Seal, Vacuum
04-17699	O-ring, 10.48ID X .139Thk, Kr
04-19101	Fitting, Tip Retainer
04-19579	Gasket, Tip .63od X .25
04-19580	Gasket, Tip, .63od X .44id
04-19581	Filter, Screen Strainer, HP Jet
04-19666	Nozzle, Spray Tip, .005 dia.
04-20028	Cylinder, Dbl, Actuating
04-20801	Indexer, SMIF, 1NX2200 W/150
04-21606	Gear Head, Planetary 20:1
04-21697	Seal, 25mm Shaft, Avalon
04-21702	Bearing, 25mm X 37mm
04-22105	Valve, Manifold, Assy.
04-22520	Valve Assy, Sol, 4Port, 2Valve
04-22992-001	Seal, Oil, .25
04-23024-001	Nozzle, Spray, .43 Orifice
04-23647-001	Flwmtr, SS, 5-55ml/min, Epr/Tef
04-23648-001	Flwmtr, SS, 15-154ml/min, Epr/Tef
04-23649-001	Flwmtr, SS, 74-745ml/min, Epr/Tef



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

04-23932-002	O-Ring, EBR #4, KR
04-23932-003	O-Ring, EBR #6, KR
04-23932-004	O-Ring, EBR #5, KR
04-24292-001	Bearing, Crossed Roller, 4.0 travel
04-25677-001	Flowmeter, 0-100cc/min, No Valve
04-25678-001	Flowmeter, 0-200cc/min, w/o valve
04-25679-001	Flowmeter, 0-600cc/Min, W/O Valve
04-25944-001	Pump, 16s,av,htm,kal,3/8cf,15ft
04-4872	Lamp House Window
05-00028	Motor,Stepper,12VDC,7.5 DEG
05-00587	Sensor, Assy, Optical
05-00704	Fan, Whisper
05-02058	Motor, Stepper
05-02561	Relay, Solid State
05-02698	Motor, Step, 12 VD
05-03020	Controller, temp, Wattlow Series 96
05-03516	Lamp, Indicator,Cal
05-06880	Switch, Vac, SPDT, 0-30'hg, 15Amp
05-11882	IC, Ram w/battery
05-12670	Motor Spin, 24V, 7.5A
05-12985	Photomicrosensor
05-13089	Microstepping Drive-IM483
05-14330-001	Battery, 80186 pcb
05-14700	Spin Controller, 200mm System
05-14915	Relay, S.S. 3-32 Cont - 280 Vac 25A Out
05-15394	Contact, Power, Female
05-15661-014	Contr, Robot, 4Axis, 1/2Rack, Upg
05-16109-002	Thermocouple, Oven/Cool. J Type, Scorpio
05-19147	Sensor Low pressure PX170-14dv
05-20678-001	SENSOR,MAGNETIC,TYPE NPN,1METR
05-22560	3Com EtherLink III ISA Combo Network adapter
05-23481	Fuse,Micro,3 Amp,Very Fast



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

05-23482	Fuse, Micro, 5 Amp, Very Fast
05-23745-001	Robot, Equipe, ATM307-2, 17.30 z
05-23850-001	Power Supply Cybor, 4 ctrls, 518
05-24065-001	Thermocouple Oven, univ tpm
05-24827-001	Transducer, 4-20ma out, 1/4mpt
05-29029-001	CNTRLR, CPS100SX, W/RESET,R-Conn
05-90004	Robot Vacuum Sensor
06-06323	E-Ring, External, .25 Shaft 06-19310 Washer, spider, valve, epr
06-22742	Spacer, Bearing
07-10613	Nozzle, Floodjet, Mod.
08-24125	OAI Probe, G-line 436nm
08-0603	Chuck low contact 8" for Theta 3
19-15459-001	Cable Assy, Rot Horz Mtr&Enc CL
19-15948-003	Earlier version of
19-23748-001	missing rear cable clamp, Refurbished
19-16137-001	Cable, Cass sens & SW a/c
19-18784-001	Cable Assy, power control to chemical cabinet, Orbitrak
19-18905-001	Cable Assy, Process Chamber to Chemical Cabinet, Interconnect
19-19061-001	Cable Assy, System to Chemical Cabinet, Orbitrak
19-19999-001	Parts Stored in Ireland
19-23748-001	Cable Assy, Phase PowerSpin #1
20-00101	Tool Box: Loaded for GCA stepper repair with special wrenches, fixtures, DVM, and other hardware.
20-00102	Oscilloscope, Tektronix, Used
24-10001-001	SSI BOM Documentation
24-13541	8500 Rev 2 Manual
24-15000-001	Manual, System 500 Supplement
24-15000-002	Manual, System 150/500 Operator's Manual
24-15000-003	Manual, System 150/500 Maintenance Manual
24-85000-001	GCA 8500 Service Manual
24-85000-002	GCA 8500 Operations Manual
24-85000-003	GCA 8500 Schematics Manual
27-17669-001	Rebuild Kit, High Pressure Pump, Haskel



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

27-22109-001	Oven Assy, plate element, housing, Insulator
28-00101	Upgrade: Wafer Size conversion to 6" wafers and Multi-Piece parts
33-25882-001	Test Fixture, Vacuum Adj, 6'
38-10002-001	Document, Reticle Handbook
44-444	Shipping & Handling
44-888	Crating Services
444-555	A-Frame, Stepper Shipping Bracket
444-999	Stepper Storage
8500-1750	G-Line Stepper 8500-1750
ACS-101	ACS Chassis with weather station.
ACS-101R	ACS chassis with weather station, old chassis must be returned.
ACS-102	Wyse, Monitor, Keyboard, Communication Cable
ACS-103	ACS with Weather station
ACS-104	ACS Chassis Non-Weather
ACS-105	Cable ACS to Compensator
ACS-106	Probe, ACS Humidity
ACS-107	Probe, ACS MT0
ACS-108	Probe, ACS MT1
ACS-109	Inline Nitrogen Filter
AFS-101	Fiber optic cable 42"
AFS-102	Lamp socket for
AFS 100	AFS-103 Column Air Regulator
AFS-104	Autofocus Lamp Power Supply (066540G1)
AFS-105	Galvo Motor, 037198G2
AFS-106	Autofocus Cable (067989G1)
AFS-107	Auto Focus Lamp Assembly
AFS-108	Galvo Motor, 067973G1
AFS-110	PCB ASSY, AU83 Preamp
AFS-111	Galvo Motor, 067973G1
AFS-202	PCB Assy, AU64
AFS-203	PC Assy, AU66
Align-101	Power Supply CCD



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

ARF-101	Autofocus subsystem
ARF-102	Dose Subassembly, Probe, Electronics Box
ARF-103	Metrology computer subassembly, Power Supplies, cabling, and Monitor
AS-201	A fork assembly
Auto-1838	GCA I-line Stepper
AWH-102	AWH1 air valve AWH-103
AWH1	Vacuum sensor
AWH-107	Cable, Transfer Arm Sensor
AWH-109	Laser Detector Assy
AWH2	100mm AWH1-102
AWH1	Microscope Power Supply
AWH2-101	Laser driver, receiver, mother pcb, Assy
AWH2-102	Motor, prealigner-T/A arm
AWH2-103	AWH Proms version 20
AWH2-104	Send Paddle AWH2 100mm
AWH2-105	AWH 2 prealign assembly
AWH2-106	Belt, AWH2 Prealign
AWH2-107	Pulse Motor Drive PCB
AWH2-108	Laser Emitter Assy 100mm
AWH2-109	Laser Detector Assy AWH2 100mm
AWH2-110	Send Robot Assy 045288
AWH2-111	MotorAWH2 Elevator 047739
AWH2-112	AWH Subcontroller
AWH2-112R	Rebuild AWH Subcontroller
AWH2-113	Cable Assy Send Robot Sensor 067400
AWH2-114	Vacuum Sensor 045304
AWH2-115	Air Regulator, AWH Subcontroller
AWH2-116	Cable, LS29b to receive puck
AWH2-117	Cable, C33R C34R C35R to C18P C19P C20P
AWH2-118	Bearing, AWH2 Robot
AWH2-119	PC Assy Sub I/O AWH (045318)
AWH2-120	PC Assy, Sub CPU AWHII (045317)



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

AWH2-121	Power Supply AWH -24v, -5v (045325)
AWH2-122	T/A emitter and detector Assembly LS5
AWH2-201	AWH2 chassis with all PCB's
AWH2-202	Prealign detector, emitter, Assembly..Includes LS1, LS2, LS3, LS4
AWH2-306	AWH Subcontroller pneumatic Hose Replacement
AWH2-311	Photo sensor and cable LS34
AWH2-312	Photo sensor and cable LS35, LS36
AWH2-313	Photo sensor and cable LS22, LS23
AWH2-314	PCB, Microscope Lamp PWS
AWH2-315	Cable, sub-controller to patch box
AWH2-316	Robot, AWHII Receive (02085801)
AWH2-317	Transfer Arm Assy, AWH2 (refurbished)
AWH2-318	Cable, Transfer Arm Clutch, LS17 to LS31, LS32 067404
AWH3-101	AWH3 send elevator cable
AWH3-102	Photo Sensor, T/A Height
AWH3-103	Belt, AWH3 Prealign
AWH3-104	Prealign Laser/Det Assy 150mm
AWH3-105	Paddle Send 150mm AWH3
AWH3-106	Paddle Receive 150mmAWH3
AWH3-107	Laser Detector Assy, AWH3 100mm
AWH3-108	Paddle, Send AWH3B 100mm
AWH3-109	Paddle, Receive AWH3B 100mm
AWH3-110	AWH Chassis with all pcb's
AWH3-111	AWH3, Transfer arm sensor cable #1 (067508)..
AWH3-112	AWH3, Transfer arm sensor cable #2 (067510)..
AWH3-113	AWH3, Prealignment sensor cable (067509)
AWH3-114	Stepper Motor AWHIII with Gear for T/A (047735)
AWH3-125	PCB, Stepper Motor Drive (045319)
AWH3-126	Vacuum solenoid
AWH3-201	Paddle Modification Includes:..Switch Box..Theta Plate..6 paddles of varying sizes..
AWH3-202	Transfer Arm Assembly (refurbished)
AWH3-203	Clutch, Micro AWH T/A + TT (045298)

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

<u>Part Number</u>	<u>Description</u>
AWH3-204	Back Lash Gear T/A Assembly (USED)
AWL-101	Motor, AWLII leveling 037050G1
AWL-103	Motor, Thetall, Rotation
AWL-104	AWL-104 Motor, Thetalll, Rotation
AWL-201	Theta II Stage
Cam-101	Microscope Objective
Cam-102	Microscope Corner Mirror
Cam-103	Sierra Camera Head
Cam-104	Microscope Reticle Objective
Cam-106	CCU 1023 Style
CCD-101	CCD Camera Upgrade
CCD-102	CCD Camera 72S W/AGC
CCD-103	CCD Camera Power Supply
Cham-101	TCC 067621G3
Cham-102	TCM 02019306
Cham-103	HVAC Unit, XLS
Cham-104	XLS Chamber
Cham-105	HVAC Unit, XLS
Cham-106	Chamber HEPA Filter
Cham-107	Switch, HVAC Blower
CHAM-108	Chamber Control Unit
Comp-103	Computer DEC 11/53 W/O PCB's
Comp-107	DEC 11/53 Computer with PCB boards
Comp-107R	DEC 11/53 Computer With PCB's, Rebuild
Comp-109	Pcb, Boot Control, DEC,11/53
Comp-110	DEC, Floppy Disk Drive
Comp-111	MTI Tape Drive, 3 tapes
Comp-501	HP Compensator, 5510A
Cym-101	Cymer Laser, model 4000 as-is
Cym-102	Shutter, Cymer (R04-06120-05)
DFAS-101	Photo Multiplier Tube 047707G1
DFAS-102	Power Supply DFAS / Insitu



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

DFAS-103	DFAS Cable, Rack-stepper-Back Panel
DFAS-104	Cable, DFAS Internal Rack (068765G1)
DFAS-108	DFAS, Monitor GCA - 9 pin
DFAS-110	Hard Disk Drive Controller for IBM Computer and HD SST225
DFAS-111	DFAS Computer IBM
HVAC-101	HVAC Blower Motor 1/3hp
IAS-101	IAS Chassis with all PCB boards
IAS-102	Muffin Fan 115V 5" for IAS Chassis
IAS-103	PC ASSY IAS HSDL Interface (043023G1)
IAS-201	Zip-Array process pcb's set of four
IAS-204	Zip-Array process pcb #3
IAS-205	Zip-Array Process PCB #4
IAS-206	PC ASSY, Zip Base Memory (039997)
IAS-207	IAS Power Supply
Int-101	Interface Power Supply 15V 045196G3
Int-102	AU79 PCB 068222G1
Int-103	Interface Chassis with all PCB's
Int-104	AU79 PCB 047763G1
Int-105	Power Supply, 5VDC (00159202)
Int-106	AU60A interface PCB (005908G2)
Int-107	AU57A Interface PCB (005878G1)
Int-108	AU59, Laser Conditioning PCB, Interface
Int-109	Interface Power Supply 5VDC
Int-110	AU58 interface PCB
J40-218-9634	Vacuum Switch, 04-00278
Las-102	HP laser Transducer 5501B
Las-103	Replacement Stage Laser Upgrade with..stand alone power supply
LAS-105	Tool, Laser Alignment
Laser-101	HP Laser Receiver
Maxi-101	Anode cable
Maxi-102	Microswitch, Maximus Housing
Maxi-103	Cylindrical Lens



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

Maxi-104	RTD Probe w/horseshoe 068391G1
Maxi-105	Mirror, M1 I-line
Maxi-106	Window, Lamp House
Maxi-107	Filter, Narrow Band I-line
Maxi-108	Lens, C1 Plano I-line
Maxi-109	Mirror, Ellipsoidal I-line
Maxi-110	Mirror, M2 I-line
Maxi-111	Mirror, M1 G-Line
Maxi-112	Maximus 2000 I-line Power Supply 02103523
Maxi-113	Maxi 1k i-line narrow band filter 039856
Maxi-114	Thermal couple cable 02122806
Maxi-115	Shutter Solenoid
Maxi-116	C1 I-Line Assy, Maxi 2000 (043412G2)
Maxi-117	Temperature Control PCB
Maxi-118	Cathode cable, Maxi 2000
Maxi-119	Ignitor Box, Maxi 2000
Maxi-120	Power Cable, Ignitor to PWS (067585G1)
Maxi-121	Power Supply, Maximus 1000
Maxi-122	Cable, Ground Maxi 2000, 045969G1
Maxi-123	Set of I-line Maximus Glass optics includes:..M1 Mirror..M2 dichroic..C1 cell..Window, Lamp House
Maxi-124	Ellipsoidal I-line
Maxi-125	Shutter Blade, Maxi 2K
Maxi-126	Shutter Bumper, Maxi 2K
Maxi-127	Thermal Couple Cable 25 ft.
Maxi-128	Cable, 1000W Lamp Anode
Maxi-129	Apodizor
Maxi-130	Timer, Mechanical, with Reset
Maxi-131	Bearing Cone
Maxi-132	Bearing Cup
Maxi-133	Mirror, M4 G-line
Maxi-134	Fiber Bundle, Maxi 1K, 006531G2



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

Maxi-135	Doublet Assy
Maxi-136	Filter, Dichroic, Maxi 1K
Maxi-137	Maxi2K Lamp Stage 067220G3
Maxi-138	Heat Sink for Arc Lamps
Maxi-201	Maxi 2000 Power Supply G-line GCA# 067087..
Maxi-202	Maximus 1000
Maxi-203	1000 Watt I-line Lamp (IC HASH 1000G)
Maxi-204	Mercury Arc Lamp, USH-1000FGIL2
Maxi-205	Lamp, Mercury Arc Lamp I-line..USH-1000FGI
Maxi-206	Mercury Arc Lamp, USH-1000FGLS
Maxi-207	Lamp, Mercury Arc Lamp I-line..USH-1000FGL3
Maxi-302	Fiber Bundle Maxi 1000 (006531G2)
Maxi-303	Fiber Bundle Maxi 1000 (006531G4)
Maxi-304	Narrow Band Filter G Line (039918)
Maxi-305	Cable Assembly GND Lamp
Maxi-306	Digital Thermometer and Cable
Met-103	Metrology Computer Upgrade for AutoStep
Mon-101	Monitor, CGA
Mon-102	Monitor, VGA DFAS
Mon-103	Monitor, DEC VT340
Mon-104	Video Mux PCB, 044915G3
Mon-105	VT100, 525 PCB, 036702G2
O5-00484	Motor, Brushless, 24 VDC, 4A, 3 PHASE
PCC-101	Power Control Center, XLS
PPC-102	PPC A/D power supply PCB 047408G1
PPC-103	Piezo PPCII
PPC-104	PPC Power Supply, 006568G2
PPC-105	PPC Electrical Box
R02-02770-002	Repair Cup Assembly DEV 150mm..Replace Base Bottom Rinse (13-02694-003) ..
R02-10002	Refurbished PCB ASSY, 44/10 W/RAM
R02-10003	Orion Thermal Fresh ..Temperature and Humidity Controller..Model AP-750FSK-DW
Rack-101	Monitor, Single rack



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

Rack-101R	Rebuild single rack monitor.
Rack-102	Monitor, Single Rack, white, no auto/text
Rack-103	Keyboard Single Rack 036517
Rack-106	VT100 PCB
Rack-107	Transformer and Distribution Box
Rack-108	Muffin Fan 115vac 12mm
Rack-109	Fan, RMS 3"
Rack-110	Fan, Computer, 4" 10vdc
Rack-111	Keyboard Cable
Rack-112	Monitor, DEC VT340
Ret-101	Reticle, Setup, 482509002, 250mil
Ret-102	Reticle, DFAS, 4800-045
RET-103	AFS-Masks
Ret-104	Reticle, Setup-01, 480009002, 90mil
Ret-105	Reticle, DFAS, 4800-024
Ret-106	Reticle, DFAS 4800-044
Ret-107	Reticle, Resolution 20mm
Ret-108	Reticle, DFAS 4800-003
RMS-101	RMS Proms version 5.01
RMS-102	RMS Main Cable
RMS-103	Reticle Cassette 90 mil
RMS-104	Coupling, Aligner Motor
Rms-105	RMS Fork and TT cable upgrade
RMS-106	Barcode Reader Assy 028634G1
RMS-107	RMS Elevator Motor (028497G1)
RMS-108	PCB, RMS Turntable Control (028875G2)
RMS-109	PCB, Elevator Control (028964G2)
RMS-110	Sensor, Turntable Align Sensor (028744G1)
RMS-111	RMS Power Supply 028522G1
RMS-112	Cable Assy A-Fork Microswitch
RMS-113	Vacuum Clamp Air Solenoid
RMS-114	RMS Pneumatics PCB



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –


Part Number

Description

RMS-115	Cable Assy B-Fork Microswitch
RMS-116	Pneumatic Box, RMS
RMS-117	RMS Align Motor (005527G1)
RMS-118	Cable, RMS Turntable
RMS-119	PCB, RMS CPU
RMS-120	RMS Chassis with all PCB's and PWS
RMS-121	RMS Preamp PCB
RMS-122	Bfork Extend Sensor
RMS-123	Cassette Door Cylinder
RMS-124	Turntable motor and cable assembly 028495G1
RMS-125	PCB, RMS Align Driver (028881G1)
RMS-126	PCB, RMS Align Control (028878G1)
RMS-127	Fork Motor 028123G2
RMS-128	25ft 37pin RMS ribbon cable
RMS-129	Motor, RMS Aperture 028944G1
RMS-130	Front Emitter, 90mil, DFAS, 115mm (047678G1)
RMS-131	Reticle, Setup-01, .25", 482509002
RMS-132	Cable, RMS Crunch Detector
RMS-133	Flag assembly, RMS Cassette
RMS-134	Turntable Swivel Bracket with Cable
RMS-135	Belt, RMS Turntable Fork (028159)
RMS-136	RMS Aperture, Micro Switch Cable
RMS-137	PCB, RMS Aperture Driver (028839G1)
RMS-144	XL Aperature Blade Sensor
RMS-145	PCB, RMS Computer INTCON 028530G1
RMS-146	T-Pot RMS TT Motor
RMS-202	RMS Sub Assy
RMS-203	RMS Turntable Assembly
RMS-204	Elevator Lead Screw upgrade
RMS-205	Fork Assy, RMS, 'B'
RMS-206	RMS Power Supply SW +5V 30A 150W
RMS-207	RMS I/O Board



STEPPER CARE SERVICES, INC.



Office – (512) 971-1531
Fax – (512) 312-5977
Email - SSIParts@austin.rr.com

Master Parts List

Printable Data Page

January 2016

– Call for Pricing –

Part Number

Description

RMS-208	Cable, Ribbon, RMS I/O
RMS-301	RMS pneumatic hose and TT cable Upgrade
RMS -116	Pneumatic Box, RMS
S99-9000	IDI Parts
Stage-101	Oil, Fine Instrument 32oz
stage-103	X-Stage Motor 035281G2
Stage-104	Y-Stage Motor 035282G2
Stage-105	Chuck, AWH3 Low Contact 100mm
Stage-106	Custom made low contact chuck.
Stage-107	Accelerometer Cable 20'
Stage-108	Accelerometer Cable 4'
Stage-116	Stage/Servo Chassis
Stage-117	Cable Servo J33 to Int AU60 J4
Stage-118	Cable Servo J32 to Int AU60 J6
Stage-119	Wafer Chuck 6" low contact, no cutout
Stage-120	Chuck, AWH1
Stage-121	Motor Y-stage 8" 046977G1
Stage-122	Pinion Gear, X
Stage-123	Pinion Gear, Y
Stage-124	Bumpers, X-Stage
Stage-125	Cable, P2
Stage-126	AWH II Piece Part Chuck
Stage-127	AWH II Piece Part Chuck, aluminum
Stage-128	AU54 Stage PCB
Stage-129	Accelerometer with 4 ft. Cable
Stage-710	Motor, X-Piezo, XLS
TMC-101	Isolation Module Assembly
TMC-102	Valve, Table Leg Air Regulator
TMC-103	Filter, Nitrogen, .05 Micron
Tool-101	Button Gauge
Tool-102	Indiac Base
Tool-103	Starrett Indiac
Tool-104	Theta 1, standoff Fixtures

